Product data sheet

Specifications





Wall mounted steel enclosure, Spacial S3D, plain door, with mounting plate, 500x400x200mm, IP66, IK10

NSYS3D5420P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 128.98 USD

Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	19.69 in (500 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	7.87 in (200 mm)
Door Type	Solid
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 mounting plate 1 door with lock 1 cable gland plate

Complementary

Body Type	Single piece body Gutter-shaped front rail double sheet thickness
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel Mounting plate galvanised steel
Surface Finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	UL cUL GL LR DNV BV
Net Weight	23.28 lb(US) (10.56 kg)

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480159442
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.65 in (24.5 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	20.28 in (51.5 cm)
Package 1 Weight	23.28 lb(US) (10.56 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	30
Package 2 Height	66.93 in (170.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	736.34 lb(US) (334.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations