Product data sheet

Specifications





Wall mounted steel enclosure, Spacial S3D, transparent door, without mounting plate, 500x400x200mm, IP66, IK08

NSYS3D5420T

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 149.35 USD

Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	19.69 in (500 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	7.87 in (200 mm)
Door Type	Glass
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock 1 cable gland plate

Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 mm double-bar lock
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body steel Door steel and security glass
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

BV
 LR

Environment

Electromagnetic Compatibility	Electromagnetic field immunity test
Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK08 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480159435
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.65 in (24.5 cm)
Package 1 Width	16.54 in (42 cm)
Package 1 Length	20.28 in (51.5 cm)
Package 1 Weight	18.85 lb(US) (8.548 kg)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	30
Package 2 Height	66.93 in (170 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	604.07 lb(US) (274 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations