

Product data sheet

Specifications



Spacial S3DB .
H250xW400xD150. IP66, IK10,
RAL7035. No

NSYS3DB25415

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 100.70 USD

Main

Range	Spacial
Product Name	Spacial S3DB
Application	Terminal application
Category	Compact enclosure
Enclosure Nominal Height	9.84 in (250 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	5.91 in (150 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Horizontal or vertical position Wall-mounting
Product Destination	For equipping with terminal
Device Composition	1 body 1 door 1 lock

Complementary

Body Type	Single piece body Gutter-shaped front rail double sheet thickness
Number Of Doors	Front face 1
Door Opening Side	Reversible 180 °)
Lock Type	3 mm double-bar lock
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	steel
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cUL LR GL UL BV DNV
Net Weight	9.11 lb(US) (4.13 kg)

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480158810
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.50 in (16.5 cm)
Package 1 Width	7.68 in (19.5 cm)
Package 1 Length	16.34 in (41.5 cm)
Package 1 Weight	9.22 lb(US) (4.18 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	84
Package 2 Height	82.68 in (210.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	813.51 lb(US) (369.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations