# Product data sheet

Specification





# Spacial S3DB H500xW400xD150. IP66, IK10, RAL7035. No

NSYS3DB5415

! Discontinued on: Sep 30, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	Spacial
Product Name	Spacial S3DB
Application	Terminal application
Category	Compact enclosure
Enclosure Nominal Height	19.69 in (500 mm)
<b>Enclosure Nominal Width</b>	15.75 in (400 mm)
Enclosure Nominal Depth	5.91 in (150 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting Horizontal or vertical position
Product Destination	For equipping with terminal
Device Composition	1 body 1 door 1 lock

## Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face 1
Door Opening Side	Reversible 180 °)
Lock Type	3 mm double-bar lock
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	steel
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	BV DNV GL UL LR cUL

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight 15.84 lb(US) (7.186 kg)

### **Environment**

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480158735
Returnability	No
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.87 in (20.0 cm)
Package 1 Width	16.34 in (41.5 cm)
Package 1 Length	20.08 in (51.0 cm)
Package 1 Weight	15.84 lb(US) (7.186 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	36
Package 2 Height	82.28 in (209.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	599.66 lb(US) (272.0 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations