

Product data sheet

Specifications



Wall mounted steel enclosure,
Spacial S3DC, plain door, without
plain chasis, 600x400x200mm,
IP66, IK10

NSYS3DC6420

Product availability: Stock - Normally stocked in distribution facility

Price*: 167.92 USD

Main

Range	Spacial
Product Name	Spacial S3DC
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	23.62 in (600 mm)
Enclosure Nominal Width	15.75 in (400 mm)
Enclosure Nominal Depth	7.87 in (200 mm)
Door Type	Solid
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock

Complementary

Body Type	Single piece body Gutter-shaped front profile double sheet thickness
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, screw driver insert
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	steel
Surface Finish	epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	UL
Net Weight	25.13 lb(US) (11.4 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP66 IEC 60529

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480314070
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.04 in (25.5 cm)
Package 1 Width	16.34 in (41.5 cm)
Package 1 Length	27.17 in (69 cm)
Package 1 Weight	25.13 lb(US) (11.4 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	24
Package 2 Height	72.05 in (183 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	637.14 lb(US) (289 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations