Product data sheet

Specifications





Spacial S3HF H800xW600xD300 EMC-immunity IP55 RAL7035

NSYS3HF8630P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,185.80 USD

Main

| Range | Spacial |
|-----------------------------|--|
| Product Name | Spacial S3HF |
| Application | Industrial Application |
| Category | Compact enclosure |
| Enclosure Nominal Height | 31.50 in (800 mm) |
| Enclosure Nominal Width | 23.62 in (600 mm) |
| Enclosure Nominal Depth | 11.81 in (300 mm) |
| Door Type | Solid |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Without gland plate |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 1 door with lock 1 mounting plate |

Complementary

| Body Type | Single piece body |
|-----------------------------|--------------------------------|
| Number Of Doors | Front face 1 |
| Lock Type | 3 points lock, 3 mm double-bar |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges |
| Material | Body aluzinc |
| Surface Finish | epoxy-polyester powder |
| Color | Gray RAL 7035) |
| Standards | IEC 60529 |
| Net Weight | 70.55 lb(US) (32 kg) |

Environment

| Electromagnetic Compatibility | EMC immunity |
|-------------------------------|----------------|
| Ik Degree Of Protection | IK10 IEC 62262 |
| In Degree Of Protection | IP55 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| Category | US10ES180035 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480212789 |
| Returnability | No |
| Country Of Origin | ES |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 32.10 in (81.534 cm) |
| Package 1 Width | 14.50 in (36.83 cm) |
| Package 1 Length | 23.60 in (59.944 cm) |
| Package 1 Weight | 69.84 lb(US) (31.679 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |