## Product data sheet

Specifications





# Wall mounted enclosure, Spacial S3X, stainless steel 304L, plain door, 1200x800x300mm, IP66

NSYS3X12830

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 1,522.30 USD

### Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	47.24 in (1200 mm)
Nominal Width	31.50 in (800 mm)
Nominal Depth	11.81 in (300 mm)
Product Installation	Wall-mounting
Device Composition	1 body 1 reinforcement frame drilled door 1 door 2 lock door

## Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Solid
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface Finish	Body and door Scotch-Brite® brushed Lock chromium plated
Net Weight	94.80 lb(US) (43 kg)

#### Environment

Standards

IEC 62208

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Certifications	UL 508 type A CAN/CSA 22
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Environmental Characteristic	Corrosive Specific hygiene

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480155017
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.60 in (32.000 cm)
Package 1 Width	31.89 in (81.000 cm)
Package 1 Length	47.64 in (121.000 cm)
Package 1 Weight	95.79 lb(US) (43.451 kg)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	4
Package 2 Height	62.99 in (160.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	411.83 lb(US) (186.804 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations