Product data sheet

Specifications





Metal industrial box plain door H150xW300xD120 IP66 IK10 RAL 7035

NSYSBM153012

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 58.81 USD

Main

Range	Spacial
Product Name	Spacial SBM
Device Application	Multi-purpose
Category	Industrial box
Device Short Name	SBM
Enclosure Type	Flat face box
Enclosure Nominal Height	5.91 in (150 mm)
Enclosure Nominal Width	11.81 in (300 mm)
Enclosure Nominal Depth	4.72 in (120 mm)
Enclosure Mounting	Wall mounted
Device Composition	4 cover screw 1 cover 1 body
Body Type	Single piece body folded and welded
Type Of Front Cover	Plain door
Cover Fixing	Half turn metal screw
Lock Type	Captive screw PZ2 outside sealed area
Removable Parts	Cover by captive screws

Complementary

Material	sheet steel
Surface Finish	Polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	LR DNV-GL UL BV
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Storage	-31140 °F (-3560 °C)
Operating Temperature	-31176 °F (-3580 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Net Weight

Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480520129
Returnability	Yes
Country Of Origin	IN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.51 in (14.0 cm)
Package 1 Width	6.38 in (16.2 cm)
Package 1 Length	12.20 in (31.0 cm)
Package 1 Weight	5.03 lb(US) (2.282 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	180
Package 2 Height	47.24 in (120 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	66.14 in (168 cm)
Package 2 Weight	855.39 lb(US) (388 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations