# **Product data sheet**

Specification





# Spacial SF enclosure without mounting plate - assembled - 2000x1000x800 mm

NSYSF201080

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,740.23 USD

### Main

Range	Spacial
Extended Range	Spacial SF
Application	Multi-purpose
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	78.74 in (2000 mm)
Enclosure Nominal Width	39.37 in (1000 mm)
Enclosure Nominal Depth	31.50 in (800 mm)
Enclosure Mounting	Floor-standing
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle door 1 rear panel 1 roof

### Complementary

Structure Type	Panels and doors built into the structure Vertical uprights joined with top and bottom frames Formed from a single section Perforated structure with a pitch of 25 mm
Door Opening Side	Reversible 120 °)
Door Type	Solid front
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Number Of Doors	Front 1
Accessibility For Operation	Rear Front Sides of enclosure
Removable Parts	Door by screws hinge Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Material	Frame galvanised steel Uprights galvanised steel Door sheet steel Panels sheet steel Hinge zamak Handle polyamide 6 with 30 % fibre glass
Surface Finish	epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)
Net Weight	296.79 lb(US) (134.62 kg)

## **Environment**

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

## Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485118420
Returnability	No
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.04 in (89.0 cm)
Package 1 Width	41.14 in (104.5 cm)
Package 1 Length	83.86 in (213.0 cm)
Package 1 Weight	282.19 lb(US) (128.0 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations