# **Product data sheet**

Specifications





# Spacial SM compact enclosure with mounting plate - 1800x1600x400 mm

NSYSM1816402DP

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,142.01 USD

## Main

Range	Spacial
Product Name	Spacial SM
Product Or Component Type	Compact enclosure
Application	Multi-purpose
Installation Accessory Type	Floor-standing
Device Composition	1 body 2 door 2 cable gland plate 1 locking system with handle door 1 blocking system left door 4 mounting plate bracket 1 mounting plate
Removable Parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure Nominal Height	70.87 in (1800 mm)
Enclosure Nominal Width	62.99 in (1600 mm)
Enclosure Nominal Depth	15.75 in (400 mm)

## Complementary

Number Of Doors	Front 2
Door Opening Side	Left 120 °) Right 120 °)
Door Type	Solid
Lock Type	4 points lock, handle with 5 mm double bar insert
Body Type	Front part forming a rigid frame with welded corners Single piece body with welded rear panel
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Cable Entry	1 entry
Material	Mounting plate galvanised steel Body sheet steel Door sheet steel Hinge zamak
Surface Finish	epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Accessibility For Operation	Front
Net Weight	443.13 lb(US) (201 kg)

## **Environment**

Standards	IEC 62208
Product Certifications	BV DNV UL
Ik Degree Of Protection	IK10 IEC 62262
Ip Degree Of Protection	IP55 IEC 60529

## Ordering and shipping details

Ooto warm.	110405040005
Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485120294
Returnability	No
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	75.98 in (193.0 cm)
Package 1 Width	64.76 in (164.5 cm)
Package 1 Length	19.29 in (49.0 cm)
Package 1 Weight	443.13 lb(US) (201.0 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations