Product data sheet

Specifications





SMX 304L stainless monobloc enclosure, H1800xW600xD400mm, Scotch Brite® finish.

NSYSMX18640

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 5,658.99 USD

Main

Range	Spacial
Product Name	Spacial SMX
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	70.87 in (1800 mm)
Nominal Width	23.62 in (600 mm)
Nominal Depth	15.75 in (400 mm)
Product Installation	Floor-standing
Device Composition	1 body 1 cable gland plate 1 locking system with handle door 4 mounting plate bracket 1 door

Complementary

Single piece body folded and welded Solid Reversible 120 °)
Reversible 120 °)
-
Front face 1
3 points lock, handle with 5 mm double-bar insert
Plain
Front
Without mounting plate
Body and door stainless steel 304L Handle zamak Hinge stainless steel
Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Enclosure Scotch-Brite® brushed Handle painted
187.39 lb(US) (85 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Product Certifications	CAN/CSA 22 UL 508
Environmental Characteristic	Corrosive Specific hygiene

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480155796
Returnability	No
Country Of Origin	BG

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	75.98 in (193.0 cm)
Package 1 Width	25.59 in (65.0 cm)
Package 1 Length	18.90 in (48.0 cm)
Package 1 Weight	187.39 lb(US) (85.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

C R & Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations