Product data sheet

Specification





PC box IP66 IK08 RAL7035 Int.H175W105D80 Ext.H192W121D87 opaque PC cover H20

NSYTBP19128

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 36.72 USD

Main

| Range | Thalassa |
|---------------------|--|
| Product Name | Thalassa TBP |
| Device Application | Multi-purpose |
| Category | Industrial box |
| Height | 7.56 in (192 mm) |
| Width | 4.76 in (121 mm) |
| Depth | 3.43 in (87 mm) |
| Internal Height | 6.89 in (175 mm) |
| Internal Width | 4.13 in (105 mm) |
| Internal Depth | 3.15 in (80 mm) |
| Enclosure Mounting | Wall mounted |
| Device Composition | 1 body 1 cover 4 cover screw |
| Quantity Per Set | Set of 2 |
| Body Type | One piece moulded |
| Type Of Front Cover | Low plain cover |
| Cover Fixing | Plastic screws |
| Lock Type | Captive screw flat outside sealed area |
| Removable Parts | Cover by captive screws |

Complementary

| Material | polycarbonate |
|-----------------------------|---|
| Color | Gray RAL 7035) |
| Standards | IEC 62208 UL 508 A |
| Product Certifications | TÜV UL |
| Electrical Insulation Class | Class II |
| Mounting Location | Outdoor (with canopy or shelter and anticondensation valve) |
| Net Weight | 0.74 lb(US) (0.335 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

| Ip Degree Of Protection | IP66 conforming to NEMA 4.4X |
|-------------------------------------|------------------------------|
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |
| Fire Resistance | 1760 °F (960 °C) |
| Ambient Air Temperature For Storage | 5140 °F (-1560 °C) |
| Operating Temperature | -13176 °F (-2580 °C) |

Ordering and shipping details

| Category | US10ES180033 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480165641 |
| Returnability | No |
| Country Of Origin | HU |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.43 in (8.7 cm) |
| Package 1 Width | 4.76 in (12.1 cm) |
| Package 1 Length | 7.56 in (19.2 cm) |
| Package 1 Weight | 14.67 oz (416 g) |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 336 |
| Package 2 Height | 47.24 in (120 cm) |
| Package 2 Width | 31.50 in (80 cm) |
| Package 2 Length | 53.15 in (135 cm) |
| Package 2 Weight | 359.35 lb(US) (163 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| | Toxic Heavy Metal Free | |
| | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |