Product data sheet

Specifications





PC box IP66 IK08 RAL7035 Int.H275W225D160 Ext.H291W241D168 opaque PC cover H60

NSYTBP292416H

Product availability: Stock - Normally stocked in distribution facility

Price*: 131.06 USD

Main

| Range | Thalassa |
|---------------------|--|
| Product Name | Thalassa TBP |
| Device Application | Multi-purpose |
| Category | Industrial box |
| Height | 11.46 in (291 mm) |
| Width | 9.49 in (241 mm) |
| Depth | 6.61 in (168 mm) |
| Internal Height | 10.83 in (275 mm) |
| Internal Width | 8.86 in (225 mm) |
| Internal Depth | 6.30 in (160 mm) |
| Enclosure Mounting | Wall mounted |
| Device Composition | 1 body 1 cover 4 cover screw |
| Body Type | One piece moulded |
| Type Of Front Cover | High plain cover |
| Cover Fixing | Plastic screws |
| Lock Type | Captive screw flat outside sealed area |
| Removable Parts | Cover by captive screws |

Complementary

| Material | polycarbonate | |
|-----------------------------|---|--|
| Color | Gray RAL 7035) | |
| Standards | IEC 62208 UL 508 A | |
| Product Certifications | TÜV UL | |
| Electrical Insulation Class | Class II | |
| Mounting Location | Outdoor (with canopy or shelter and anticondensation valve) | |
| Net Weight | 2.73 lb(US) (1.24 kg) | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

| Ip Degree Of Protection | IP66 conforming to NEMA 4.4X |
|-------------------------------------|------------------------------|
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |
| Fire Resistance | 1760 °F (960 °C) |
| Ambient Air Temperature For Storage | 5140 °F (-1560 °C) |
| Operating Temperature | -13176 °F (-2580 °C) |

Ordering and shipping details

| Category | US10ES180033 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480165757 |
| Returnability | Yes |
| Country Of Origin | HU |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7.09 in (18 cm) |
| Package 1 Width | 9.84 in (25 cm) |
| Package 1 Length | 12.20 in (31 cm) |
| Package 1 Weight | 3.01 lb(US) (1.367 kg) |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 4 |
| Package 2 Height | 15.75 in (40 cm) |
| Package 2 Width | 15.75 in (40 cm) |
| Package 2 Length | 23.62 in (60 cm) |
| Package 2 Weight | 14.51 lb(US) (6.58 kg) |
| Unit Type Of Package 3 | PAM |
| Number Of Units In Package 3 | 100 |
| Package 3 Height | 86.61 in (220 cm) |
| Package 3 Width | 39.37 in (100 cm) |
| Package 3 Length | 47.24 in (120 cm) |
| Package 3 Weight | 392.42 lb(US) (178 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| | Toxic Heavy Metal Free | |
| | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |