Product data sheet

Specification





ABS box IP66 IK07 RAL7035 Int.H325W275D120 Ext.H341W291D128 Opaque cover H20

NSYTBS342912

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 44.07 USD

Main

Range	Thalassa
Product Name	Thalassa TBS
Device Application	Multi-purpose
Category	Industrial box
Height	13.43 in (341 mm)
Width	11.46 in (291 mm)
Depth	5.04 in (128 mm)
Internal Height	12.80 in (325 mm)
Internal Width	10.83 in (275 mm)
Internal Depth	4.72 in (120 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 4 cover screw
Body Type	One piece moulded
Type Of Front Cover	Low plain cover
Cover Fixing	Plastic screws
Lock Type	Captive screw flat outside sealed area
Removable Parts	Cover by captive screws

Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	TÜV
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK07 conforming to IEC 62262
Glow Wire Resistance	1202 °F (650 °C) IEC 60695-2-11
Ambient Air Temperature For Storage	5104 °F (-1540 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Operating Temperature	-13140 °F (-2560 °C)
Net Weight	2.56 lb(US) (1.16 kg)

Ordering and shipping details

_	
Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480165405
Returnability	No
Country Of Origin	HU

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.51 in (14 cm)
Package 1 Width	11.81 in (30 cm)
Package 1 Length	13.98 in (35.5 cm)
Package 1 Weight	3.01 lb(US) (1.365 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	15.75 in (40 cm)
Package 2 Width	15.94 in (40.5 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	14.04 lb(US) (6.37 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	48
Package 3 Height	53.15 in (135 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	191.80 lb(US) (87 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations