# Product data sheet

Specifications





### ABS box IP66 IK07 RAL7035 Int.H65W65D45 Ext.H74W74D56 Opaque cover H10

NSYTBS775

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 8.24 USD

#### Main

Range	Thalassa
Product Name	Thalassa TBS
Device Application	Multi-purpose
Category	Industrial box
Height	2.91 in (74 mm)
Width	2.91 in (74 mm)
Depth	2.13 in (54 mm)
Internal Height	2.56 in (65 mm)
Internal Width	2.56 in (65 mm)
Internal Depth	1.85 in (47 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 4 cover screw
Quantity Per Set	Set of 5
Body Type	One piece moulded
Type Of Front Cover	Low plain cover
Cover Fixing	Metal screws
Lock Type	Captive screw flat outside sealed area
Removable Parts	Cover by captive screws

#### Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	ΤÜV
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK07 conforming to IEC 62262
Glow Wire Resistance	1202 °F (650 °C) IEC 60695-2-11
Ambient Air Temperature For Storage	5104 °F (-1540 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Operating Temperature	-13140 °F (-2560 °C)
Net Weight	0.15 lb(US) (0.068 kg)

# Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480165207
Returnability	Yes
Country Of Origin	HU

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.63 in (1.6 cm)
Package 1 Width	0.67 in (1.7 cm)
Package 1 Length	2.28 in (5.8 cm)
Package 1 Weight	2.61 oz (74 g)

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations