Specifications



# Polyester canopy for PLA enclosure W1000xD320 mm

NSYTJPLA103G

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 67.72 USD

Main		
Range		
Accessory / Separate Part Category		
Product Or Component Type		
Application		

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Сапору
Application	Multi-purpose
Range Compatibility	Thalassa Thalassa PLA
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	1 canopy fixing elements drilling template

### Complementary

	-
Material	polyester charged with fibreglass
Color	Gray RAL 7035)
Fixing Mode	By fixing element
Height	1.50 in (38 mm)
Width	39.37 in (1000 mm)
Depth	12.60 in (320 mm)

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480777356
Returnability	No
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.500 cm)
Package 1 Width	13.58 in (34.500 cm)
Package 1 Length	40.75 in (103.500 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Weight	7.81 lb(US) (3.541 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	10
Package 2 Height	17.72 in (45.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	104.52 lb(US) (47.410 kg)

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations