

# Product data sheet

Specifications



with knockouts for Spacial S3D encl.  
RAL7035, L245xW130

NSYTLCK

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

## Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D
Mounting Location	Enclosure bottom
Cable Gland Type	ISO knock-out
Cable Entry	2 knock-outs M12 5 knock-outs M16 2 knock-outs M20
Device Composition	fixing elements 1 plate 1 separate gasket
Quantity Per Set	Set of 1
Material	Plate steel Seal polyethylene (PE) foam

## Complementary

Color	Plate Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Height	9.65 in (245 mm)
Width	9.65 in (245 mm)
Depth	5.12 in (130 mm)
Thickness	0.06 in (1.5 mm)

## Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
Gtin	03606480168444
Returnability	No
Country Of Origin	FR

## Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------