Product data sheet

Specification





Spacial S3D flexicable gland plate with membrane pearcable 478 x 63 mm

NSYTLFME

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 127.23 USD

Main

Range	Spacial
Product Or Component Type	Flexicable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D
Mounting Location	Enclosure bottom
Cable Gland Type	Pierceable by screwdriver
Type Of Gland Plate	Membrane
Cable Outer Diameter	0.391.02 in (1026 mm)
Cable Entry	Without
Device Composition	1 plate membrane
Quantity Per Set	Set of 1
Material	Plate steel Membrane HCE (heat curable elastomer)

Complementary

•	
Color	Plate Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Height	1.18 in (30 mm)
Width	21.46 in (545 mm) Real 22.05 in (560 mm)
Depth	5.12 in (130 mm)
Net Weight	2.35 lb(US) (1.066 kg)
Thickness	0.06 in (1.5 mm)
Number Of Cut-Out	Undrilled
Cut-Out Dimensions	478 x 63 mm

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3606480467660
Returnability	No
Country Of Origin	SK

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	5.31 in (13.5 cm)
Package 1 Length	22.05 in (56.0 cm)
Package 1 Weight	2.50 lb(US) (1.136 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	200
Package 2 Height	31.50 in (80.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	500.89 lb(US) (227.2 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations