# **Product data sheet**

Specification





Plug-in bridge, Linergy TR, 4 pole, for 4mm² terminal blocks, red, 4 way, 6.2mm pitch, set of 50

NSYTRAL44

Product availability: Stock - Normally stocked in distribution facility

Price\*: 2.30 USD

### Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Plug-in bridge
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number Of Ways	4 ways

### Complementary

Cable Cross Section	0.01 in² (4 mm²)	
Number Of Connections	4	
	2	
	3	
Number Of Measurement Input	1	
	4	
	2	
	6	
	3	
Quantity Per Set	Set of 50	
Net Weight	0.13 oz (3.8 g)	
Color	Red	

## Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
Gtin	3606480534157
Returnability	Yes
Country Of Origin	DE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.18 in (3.000 cm)
Package 1 Width	2.76 in (7.000 cm)
Package 1 Length	5.91 in (15.000 cm)
Package 1 Weight	0.11 oz (3.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	1.18 in (3.000 cm)
Package 2 Width	2.76 in (7.000 cm)
Package 2 Length	5.91 in (15.000 cm)
Package 2 Weight	6.84 oz (194.000 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	250
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	2.58 lb(US) (1.171 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
	EU RoHS Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration