Product data sheet

Specifications





19" swing chass 20U W800 Spacial

NSYVDM20U8P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 366.89 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	19" rack
Application	Electronic application Multi-purpose
For Enclosure Nominal Dimensions	- H: 39.37 in (1000 mm) W: 31.50 in (800 mm) D: 9.84 in (250 mm) - H: 39.37 in (1000 mm) W: 31.50 in (800 mm) D: 11.81 in (300 mm) - H: 39.37 in (1000 mm) W: 31.50 in (800 mm) D: 15.75 in (400 mm)
Rack Type	Swing
Mounting Location	Front of enclosure
Range Compatibility	Spacial Spacial S3D Spacial Spacial S3X Spacial Spacial VDM Spacial Spacial CRN Spacial Spacial CRNG
Device Composition	fixing elements 1 19" swing chassis 2 lock
Number Of Units 19"	20

Complementary

Material	Chassis steel
Enclosure/Cubicle Description	Wall-mounted enclosure
Surface Finish	Epoxy-polyester powder
Lock Type	Lock with 3 mm double bar insert
Fixing Mode	By fixing element
Color	Gray RAL 7035)
Permanent Permissible Load	6.61 lb(US) (3 kg) per unit
Opening Of The 19" Racks	Reversible 120 °
Height	Nominal 39.37 in (1000 mm)
Width	Nominal 31.50 in (800 mm)
Depth	5.12 in (130 mm)
Net Weight	25.57 lb(US) (11.6 kg)

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480174742
Returnability	No
Country Of Origin	ES

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	37.40 in (95.0 cm)
Package 1 Width	32.68 in (83.0 cm)
Package 1 Length	5.12 in (13.0 cm)
Package 1 Weight	25.57 lb(US) (11.6 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations