

Product data sheet

Specifications



Busway Circuit Breaker Plug-in Unit 20A 208Y/120V 5A 6FT CORD L6-20 W/METER

PBPEDU5A100FOOL620M1

Main

Product Or Component Type	Plug-in unit
Range Of Product	Powerbus

Complementary

Line Rated Current	100 A
[Ue] Rated Operational Voltage	208Y/120 V AC
Busbar Configuration	5A L1 + IG + L2 + N + L3
Number Of Phases	3 phase
Wiring Configuration	4-wire (isolated ground and 100 percent neutral)
Circuit Breaker Type	EDU, 20 A, 2 1 breaker
Number Of Receptacles	PM5350 meter
Cable Length	Drop cable 6 ft (1.83 m)
Connector Type	L6-20

Environment

Nema Enclosure Rating	NEMA 1
Ip Degree Of Protection	IP40

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	78.74 in (200 cm)
Package 1 Width	98.43 in (250 cm)
Package 1 Length	157.48 in (400 cm)
Package 1 Weight	19.84 lb(US) (9 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications