

Product data sheet

Specifications



All In One ISO Container 75kW 12rack InRow DX 480V

PFMICC075W1N12C

Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	480 V 3 phase
Main Output Voltage	208 V 3 phase
Kw Rating	75000 W
Number Of Rack Unit	42U
Battery Type	VRLA
Provided Equipment	EcoStruxure IT ready (UPS)

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Volt-Amp-Hour Capacity	0 VAh

Physical

Color	White
Height	114.02 in (289.6 cm)
Width	95.98 in (243.8 cm)
Depth	480.00 in (1219.2 cm)
Net Weight	32959.14 lb(US) (14950 kg)
Mounting Mode	Not rack-mountable
Number Of Racks	12
Rack Free Space	504

Input

Input Frequency	60 Hz
-----------------	-------

Output

Output Frequency (Sync To Mains)	60 Hz sync to mains
Kw Per Rack	6.25 W
Pdu Type	Metered

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Configured Power	75000 W
------------------	---------

Conformance

Product Certifications	cUL Listed UL Listed
------------------------	-------------------------

Environmental

Ambient Air Temperature For Operation	-13...104 °F (-25...40 °C)
---------------------------------------	----------------------------

Operating Altitude	0...1500 ft
--------------------	-------------

Communications & Management

Emergency Power Off (Epo)	Optional
---------------------------	----------

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
