


Product data sheet

Specifications

SQUARE D

Green Premium™



Busway I-Line Fusible Plug-in Unit, 3P, 30A, 600V, with R Fuse Reject, CU Lugs

PQ3603GRA

Product availability : Stock - Normally stocked in distribution facility

Price* : 1,254.00 USD

Main

Product or Component Type Plug-in unit

Range of Product I-Line

Complementary

Protection Type Fuse

Mounting Mode Plug-in

Fuse type H, K or J

[Ue] rated operational voltage 600 V AC

Line Rated Current 30 A

Number of Phases 3 phase

Poles description 3P

Interrupt Rating 10 kA H or K
200 kA J

Wiring configuration 4-wire (integral ground bus)

AWG gauge AWG 10...AWG 2 1 ground
AWG 12...AWG 2 1 phase
AWG 12...AWG 1/0 1 neutral

Depth 4.65 in (118 mm)

Height 14.92 in (379 mm)

Width 10.47 in (266 mm)

Included Options Fuse rejection clips, class R

Environment

Product Certifications CSA C22.2 No 27
UL listed file E22182

Standards UL 857

Ordering and shipping details

Category 20177-PQ 30/60/100 FUSIBLE PLUGS

Discount Schedule PE7

GTIN 785901087236

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.80 in (24.892 cm)
Package 1 Width	11.40 in (28.956 cm)
Package 1 Length	15.50 in (39.37 cm)
Package 1 Weight	13.32 lb(US) (6.042 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)