





Circuit breaker, PowerPacT Q, 80A, 2 pole, 240VAC, 10kA, I-Line, thermal magnetic, 80%, BC

QBA220804

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 900.00 USD

Main

Panga	PowerPact
Range	PowerPact
Product Name	PowerPact Q
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

80 A	
2P	
Operating handle	
В	
10 kA 120/208 V AC 50/60 Hz UL 10 kA 240 V AC 50/60 Hz UL	
240 V AC 50/60 Hz UL	
50/60 Hz	
thstand 8 kV UL	
Thermal-magnetic	
1800 A	
1000 A	
80 %	
Category A	
1000 cycles loaded 5000 cycles no load	
1 trip indicator green)	
I-Line bracket)	
Bracket	
I-Line connection, line Lugs, load	
3 in (76.20 mm)	
que 247.82 lbf.in (28 N.m) 0.040.23 in² (25150 mm²) (AWG 4300 kcmil)	
0.87 in (22 mm)	
ght 6.47 in (164.34 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	3 in (76.20 mm)	
Depth	3.93 in (99.82 mm)	
Phase Connection	BC	
Circuit Breaker Application	HACR rated	

Environment

Standards	UL CSA NEMA NOM-003-SCFI-2000
Product Certifications	UL CSA NOM
Ambient Air Temperature For Operation	104158 °F (4070 °C)

Ordering and shipping details

Category	US10DE201023	
Discount Schedule	0DE2	
Gtin	3606487116196	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	4.25 in (10.795 cm)	
Package 1 Width	7.44 in (18.893 cm)	
Package 1 Length	12.31 in (31.275 cm)	
Package 1 Weight	4.75 lb(US) (2.155 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
Ø	Rohs Exemption Information	'es
⊘	Pvc Free	
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov