





Circuit breaker, PowerPacT Q, 125A, 3 pole, 240VAC, 25kA, lugs, thermal magnetic, 80%, top of panel

QDM32125TN

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,676.00 USD

#### Main

Range	PowerPact	
Product Name	PowerPact Q	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Line Rated Current	125 A	
Line Nateu Guirellt	125 A	
Number Of Poles	3P	
Control Type	Operating handle	
Breaking Capacity Code	D	
Breaking Capacity	25 kA 120/208 V AC 50/60 Hz UL 25 kA 240 V AC 50/60 Hz UL	
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz UL	
Network Frequency	50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	8 kV UL	
Trip Unit Technology	Thermal-magnetic	
Magnetic Tripping Current	2400 A	
Magnetic Hold Current	1200 A	
Continuous Current Rating	80 %	
Utilisation Category	Category A	
Mechanical Durability	1000 cycles loaded 5000 cycles no load	
Local Signalling	1 trip indicator green)	
Mounting Mode	Unit mount lug)	
Mounting Support	Lug	
Electrical Connection	Lugs, line Terminal nut, load	
Tightening Torque	247.82 lbf.in (28 N.m) 0.040.23 in² (25150 mm²) (AWG 4300 kcmil)	
Power Wire Stripping Length	0.87 in (22 mm)	
Height	6.47 in (164.34 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	4.5 in (114.30 mm)
Depth	3.93 in (99.82 mm)
Circuit Breaker Application	HACR rated

## **Environment**

Standards	UL
	CSA
	NEMA
	NOM-003-SCFI-2000
Product Certifications	UL
	CSA
	NOM
Ambient Air Temperature For	104158 °F (4070 °C)

## Ordering and shipping details

Category	US1DE2A00187
Discount Schedule	DE2A
Gtin	785901417217
Returnability	No
Country Of Origin	US

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

# **Contractual warranty**



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

Mercury Free	
Rohs Exemption Information Y	es
Pvc Free	
Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov