

# Product data sheet

Specifications



Mini circuit breaker, QO, 30A, 3 pole, 120/240VAC, 65kA, plug in

QH330

Product availability: Stock - Normally stocked in distribution facility

Price\*: 507.00 USD

## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

## Complementary

Interrupt Rating	65 kA 120/240 V AC 65 kA 240 V AC 65 kA 120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.83 lb(US) (0.376 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	US1DE2A00926
Discount Schedule	DE2A
Gtin	785901205548
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.40 in (6.096 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	3.80 in (9.652 cm)
Package 1 Weight	13.28 oz (376.482 g)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)  
[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Halogen Free Product	

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations