





Load center, QO, 1 phase, 12 spaces, 24 circuits, 100A convertible main breaker, PoN, NEMA1, combo cover, UL

QO112M100PC

Product availability: Stock - Normally stocked in distribution facility

Price*: 380.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Combination flush/surface cover
Provided Equipment	Cover

Complementary

Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (breaker)
Rated Current	100 A
Number Of Spaces	12
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	24
Maximum Number Of Tandem Breakers	12
Number Of Phases	1 phase
Ground Bar	Grounding bar (ordered separately)
Box Number	5
Height	14.92 in (379 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)
Net Weight	16.14 lb(US) (7.320 kg)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	III Listed

Ordering and shipping details

Category	US1DE3A10001
Discount Schedule	DE3A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	785901596318
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.70 in (44.958 cm)
Package 1 Width	16.00 in (40.64 cm)
Package 1 Length	5.70 in (14.478 cm)
Package 1 Weight	16.71 lb(US) (7.58 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov