

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 15A, 1 pole, 120VAC, 10kA, plug in, high magnetic

QO115HM320

Discontinued on: Dec 8, 2020

End-of-service on: Dec 31, 2020

Discontinued

## Main

|                       |                               |
|-----------------------|-------------------------------|
| Product               | Miniature circuit-breaker     |
| Range                 | QO                            |
| Current Rating        | 15 A                          |
| Voltage Rating        | 120 V AC                      |
| Mounting Type         | Plug-in                       |
| Number Of Poles       | 1P                            |
| Circuit Breaker Type  | High magnetic                 |
| Ratings               | HACR and Switching Duty rated |
| Electrical Connection | Pressure plate                |

## Complementary

|                        |                                    |
|------------------------|------------------------------------|
| Interrupt Rating       | 10 kA 120 V AC                     |
| Number Of Panel Spaces | 1                                  |
| Wire Size              | AWG 14...AWG 8 copper or aluminium |
| Tightening Torque      | 35.40 lbf.in (4 N.m)               |
| Height                 | 2.99 in (76 mm)                    |
| Width                  | 0.75 in (19 mm)                    |
| Depth                  | 2.91 in (74 mm)                    |
| Net Weight             | 0.42 lb(US) (0.191 kg)             |

## Environment

|                |                  |
|----------------|------------------|
| Certifications | UL Listed<br>CSA |
| Ambient Rating | 104 °F (40 °C)   |

## Ordering and shipping details

|                   |                                |
|-------------------|--------------------------------|
| Category          | 00080-QO SPECIALTY CB,1&2 POLE |
| Discount Schedule | DE2A                           |
| Returnability     | No                             |
| Country Of Origin | MX                             |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 3.20 in (8.128 cm)     |
| Package 1 Width              | 3.00 in (7.62 cm)      |
| Package 1 Length             | 0.80 in (2.032 cm)     |
| Package 1 Weight             | 0.32 lb(US) (0.145 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|