Product data sheet

Specifications



Mini circuit breaker, QO, 30A, 1 pole, 120/240VAC, 10kA, plug in, aux switch 1A

QO1301200

() Discontinued on: Jul 30, 2020

(!) End-of-service on: Sep 22, 2020

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate
Options	Auxiliary switch 120 V AC 1A

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.67 lb(US) (0.304 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00004-QO,QOT 10-30A 1P;10-60A 2P
Discount Schedule	DE2A
Returnability	No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

MX

Dooking	Ilmita
Packing	Units
1 aoning	011100

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.25 in (3.175 cm)
Package 1 Width	3.38 in (8.573 cm)
Package 1 Length	3.00 in (7.62 cm)
Package 1 Weight	10.72 oz (303.907 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)