





Mini circuit breaker, QO, 30A, 1 pole, 120/240VAC, 10kA, plug in, high density discharge

QO130HID

! Discontinued on: Jun 30, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	30 A	
Voltage Rating	120/240 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Circuit Breaker Type	High intensity discharge	
Ratings	Not rated	
Electrical Connection	Pressure plate	

## Complementary

•	
Interrupt Rating	10 kA 120/240 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	3.11 in (79 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.27 lb(US) (0.122 kg)

### **Environment**

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	US1DE2A00080	
Discount Schedule	DE2A	
Gtin	00785901543732	
Returnability	Yes	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.80 in (2.032 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	4.32 oz (122.47 g)

# **Contractual warranty**

Warranty 18 months

Apr 25, 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Product

### **Certifications & Standards**

Eu Rons Directive	Compilant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration