

Product data sheet

Specifications

SQUARE D



Load center, QO, 1 phase, 30 spaces, 30 circuits, 200A convertible main breaker, NEMA1, UL

QO130M2001021

Discontinued

Discontinued on: May 18, 2020

Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Order separately

Complementary

Tightening Torque	Cover 20 lb.in
Pon Convertible Mains (Lugs)	Main breaker
Rated Current	200 A
Number Of Spaces	30
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	30
Maximum Number Of Tandem Breakers	0
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4...250 kcmil aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	9
Height	29.84 in (758 mm)
Width	14.25 in (362 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	00001-QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.16 oz (4.536 g)

Contractual warranty

Warranty	18 months
----------	-----------