





Load center, QO, 1 phase, 40 spaces, 60 circuits, 200A convertible main lugs, PoN, NEMA3R, gnd bar, UL

QO140L200PGRB

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,338.00 USD

#### Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure
Provided Equipment	Grounding bar

# Complementary

Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)	
Rated Current	200 A	
Number Of Spaces	40	
Max Short Circuit Current Rating	65 kA	
Maximum Number Of Single Pole Circuits	40	
Maximum Number Of Tandem Breakers	20	
Number Of Phases	1 phase	
Ground Bar	Grounding bar included (not installed)	
Box Number	7R	
Height	33.78 in (858 mm)	
Width	14.76 in (375 mm)	
Depth	4.53 in (115 mm)	
Net Weight	39.90 lb(US) (18.100 kg)	

### **Environment**

Enclosure Rating	NEMA 3R outdoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

# Ordering and shipping details

Category	US1DE3A10002
Discount Schedule	DE3A
Gtin	785901086093

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	14.76 in (37.5 cm)
Package 1 Length	33.78 in (85.8 cm)
Package 1 Weight	38.45 lb(US) (17.441 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov