# **Product data sheet**

Specifications

SQUARE D





Load center, QO, 1 phase, 54 spaces, 64 circuits, 225A convertible main lugs, PoN, NEMA1, gnd bar, UL

QO154L225PG

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 1,248.00 USD

#### Main

Man		
Marketing Trade Name	QO	
Product Type	Load Center	
Cover Type	Order separately	

### Complementary

Complementary	
Tightening Torque	Main lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper Cover 20 lb.in
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)
Rated Current	225 A
Number Of Spaces	54
Max Short Circuit Current Rating	65 kA
Maximum Number Of Single Pole Circuits	64
Maximum Number Of Tandem Breakers	10
Number Of Phases	1 phase
Wire Size	AWG 6300 kcmil aluminium/copper
Ground Bar	Grounding bar included (not installed)
Electrical Connection	Lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	12
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)

### Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US1DE3A10003
Discount Schedule	DE3A
Gtin	785901316961
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.30 in (10.922 cm)
Package 1 Width	14.80 in (37.592 cm)
Package 1 Length	40.60 in (103.124 cm)
Package 1 Weight	21.78 lb(US) (9.879 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	27
Package 2 Height	43.80 in (111.252 cm)
Package 2 Width	40.60 in (103.124 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	619.00 lb(US) (280.773 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov