





Load center, QO, 1 phase, 54 spaces, 64 circuits, 225A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar, UL

QO154L225PQG



! Discontinued on: Jun 30, 2023

Product availability: Stock - Normally stocked in distribution facility

Main

Marketing Trade Name	QO
Product Type	Load Center
Provided Equipment	Qwik grip assembly kit 1)

Complementary

Tightening Torque	Main lugs 250 lb.in, AWG 4250 kcmil, aluminium/copper
Pon Convertible Mains (Lugs)	PoN Convertible Mains (lugs)
Rated Current	225 A
Number Of Spaces	54
Maximum Number Of Single Pole Circuits	64
Maximum Number Of Tandem Breakers	10
Number Of Phases	1 phase
Ground Bar	Grounding bar included (not installed)
Height	39.37 in (1000 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A10003
Discount Schedule	DE3A
Gtin	785901886617
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	39.37 in (100.0 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	22.00 lb(US) (9.979 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	27
Package 2 Height	42.00 in (106.68 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	594.00 lb(US) (269.433 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov