





Load center, QO, 1 phase, 6 spaces, 12 circuits, 125A convertible main breaker, NEMA3R, feedthru lugs, UL

QO1612M125FTRB100

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 930.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure
Cover Type	Surface cover

Complementary

Pon Convertible Mains (Lugs)	Main breaker
Rated Current	100 A
Number Of Spaces	6
Max Short Circuit Current Rating	22 kA
Maximum Number Of Single Pole Circuits	12
Maximum Number Of Tandem Breakers	6
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4AWG 2/0 aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Electrical Connection	Feed-thru lugs
Wiring Configuration	3-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded galvannealed steel
Surface Finish	Baked enamel Gray
Box Number	3R
Height	18.94 in (481 mm)
Width	14.76 in (375 mm)

Environment

Enclosure Rating	NEMA 3R outdoor
Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications UL Listed

Ordering and shipping details

Category	US1DE3A00101
Discount Schedule	DE3A
Gtin	785901651437
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.94 in (50.639 cm)
Package 1 Width	4.62 in (11.747 cm)
Package 1 Length	15.19 in (38.574 cm)
Package 1 Weight	20.82 lb(US) (9.444 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov