





Circuit breaker enclosure, QO, 1 phase, 2 spaces, 100A, NEMA1, surface cover, UL

**QO2100BNS** 

Product availability: Stock - Normally stocked in distribution

Price\*: 83.00 USD

### Main

Product Type	Enclosure
Range Of Product	QO

### Complementary

Current Rating	100 A	
Interrupt Rating	22 kA	
Number Of Spaces	2	
Maximum Number Of Single Pole Circuits	2	
Maximum Number Of Tandem Breakers	0	
Number Of Phases	1 phase	
Enclosure Rating	NEMA 1 indoor	
Breaker Compatibility	Circuit breaker QO 2P	
Product Certifications	UL Listed	
Wiring Configuration	3-wire	
Electrical Connection	Lugs	
Wire Size	AWG 14AWG 1 copper AWG 12AWG 1 aluminium	
Surface Finish	Baked enamel Gray	
Busbar Material	Tin plated copper: busbar	
Tightening Torque	35 lb.in, AWG 14AWG 10, copper 35 lb.in, AWG 12AWG10, aluminium 40 lb.in, AWG 8AWG 4, aluminium/copper 50 lb.in, AWG 3AWG 2, aluminium/copper Main lugs 50 lb.in, AWG 3AWG 1, aluminium/copper	
Box Number	13	
Cover Type	Surface cover	
Ground Bar	Grounding bar (ordered separately)	
Enclosure Material	Welded sheet steel	
Enclosure Type	Enclosure	
Height	13.11 in (333 mm)	
Width	5.87 in (149 mm)	
Depth	3.4 in (86.36 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US1DE2A00005	
Discount Schedule	Schedule DE2A	
Gtin	785901051732	
Returnability	Yes	
Country Of Origin	MX	

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	4.61 in (11.7 cm)	
Package 1 Width	7.40 in (18.8 cm)	
Package 1 Length	15.00 in (38.1 cm)	
Package 1 Weight	5.67 lb(US) (2.57 kg)	
Unit Type Of Package 2	Package 2 PAL	
Number Of Units In Package 2	135	
Package 2 Height	ght 40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	781.70 lb(US) (354.574 kg)	

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov