





Circuit breaker enclosure, QO, 1 phase, 2 spaces, 125A, NEMA3R, UL

QO2125BNRB

Product availability: Stock - Normally stocked in distribution facility

Price*: 158.00 USD

Main

Product Type	Enclosure
Range Of Product	QO

Complementary

Current Rating	125 A
Interrupt Rating	22 kA
Number Of Spaces	2
Maximum Number Of Single Pole Circuits	2
Maximum Number Of Tandem Breakers	0
Number Of Phases	1 phase
Enclosure Rating	NEMA 3R outdoor
Breaker Compatibility	Circuit breaker QO 2P
Product Certifications	UL Listed
Wiring Configuration	3-wire
Electrical Connection	Lugs
Wire Size	AWG 12AWG 2/0 aluminium AWG 14AWG 2/0 copper
Surface Finish	Baked enamel Gray
Busbar Material	Tin plated copper: busbar
Tightening Torque	35 lb.in, AWG 14AWG 10, copper 35 lb.in, AWG 12AWG10, aluminium 40 lb.in, AWG 8AWG 4, aluminium/copper 50 lb.in, AWG 3AWG 2, aluminium/copper Main lugs 50 lb.in, AWG 3AWG 2/0, aluminium/copper
Box Number	13R
Ground Bar	Grounding bar (ordered separately)
Enclosure Material	Welded galvannealed steel
Enclosure Type	Enclosure
Height	16.18 in (411 mm)
Width	6.93 in (176 mm)
Depth	4 in (101.60 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE2A00005
Discount Schedule	DE2A
Gtin	785901051800
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	17.91 in (45.5 cm)
Package 1 Weight	9.59 lb(US) (4.35 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov