





# Mini circuit breaker, QO, 15A, 2 pole, 120/240VAC, 10kA, plug in

QO215

Product availability: Stock - Normally stocked in distribution facility

Price\*: 67.00 USD

## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

# Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.60 lb(US) (0.272 kg)

## **Environment**

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

# Ordering and shipping details

Category	US1DE2A00004
Discount Schedule	DE2A
Gtin	785901400301
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	8.64 oz (244.94 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	2.70 in (6.858 cm)
Package 2 Length	7.70 in (19.558 cm)
Package 2 Weight	2.72 lb(US) (1.234 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	8.40 in (21.336 cm)
Package 3 Width	7.40 in (18.796 cm)
Package 3 Length	17.50 in (44.45 cm)
Package 3 Weight	28.05 lb(US) (12.723 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>Ø</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov