





# Mini circuit breaker, QO, 70A, 2 pole, 120/240VAC, 10kA, plug in

QO270H

- ! Discontinued on: Dec 8, 2020
- ! End-of-service on: Dec 31, 2020



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	70 A	
Voltage Rating	120/240 V AC 240 V AC 120 V AC	
Mounting Type	Plug-in	
Number Of Poles	2P	
Circuit Breaker Type	Standard	
Ratings	HACR rated	
Electrical Connection	Box lugs	

## Complementary

<u> </u>	
Interrupt Rating	10 kA 120/240 V AC
	10 kA 240 V AC
	10 kA 120 V AC
Number Of Panel Spaces	2
Wire Size	AWG 8AWG 2 copper or aluminium
Tightening Torque	49.56 lbf.in (5.6 N.m)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.75 lb(US) (0.340 kg)

### **Environment**

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

# Ordering and shipping details

Category	US1DE2A00926
Discount Schedule	DE2A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	00785901088318
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	3.80 in (9.652 cm)
Package 1 Weight	0.75 lb(US) (0.34 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>②</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>②</b>	Halogen Free Product

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration