





Load center, QO, 1 phase, 2 spaces, 2 circuits, 40A fixed main lugs, NEMA3R, UL

QO2L40RB

Product availability: Stock - Normally stocked in distribution

Price\*: 113.00 USD

### Main

Marketing Trade Name	QO
Product Type	Load Center
Enclosure Type	Weatherproof enclosure
Cover Type	Surface cover

### Complementary

Tightening Torque	Main lugs 35 lb.in, AWG 14AWG 10, aluminium/copper Main lugs 40 lb.in, AWG 8AWG 4, aluminium/copper Main lugs 35 lb.in, AWG 12AWG10, aluminium/copper	
Pon Convertible Mains (Lugs)	Fixed Mains (lugs)	
Rated Current	40 A	
Number Of Spaces	2	
Max Short Circuit Current Rating	65 kA	
Maximum Number Of Single Pole Circuits	2	
Maximum Number Of Tandem Breakers	0	
Number Of Phases	1 phase	
Voltage Rating	120/240 V AC	
Wire Size	AWG 14AWG 6 copper AWG 12AWG 6 aluminium	
Ground Bar	Grounding bar (ordered separately)	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Busbar Material	Tin plated aluminium: busbar	
Enclosure Material	Welded galvannealed steel	
Surface Finish	Baked enamel Gray	
Box Number	1R	
Height	9.37 in (238 mm)	
Width	4.88 in (124 mm)	

### **Environment**

**Enclosure Rating** NEMA 3R outdoor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)
Product Certifications	III Listed

# Ordering and shipping details

Category	US1DE3A00101
Discount Schedule	DE3A
Gtin	785901785118
Returnability	Yes
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	6.20 in (15.748 cm)
Package 1 Length	11.20 in (28.448 cm)
Package 1 Weight	5.16 lb(US) (2.34 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	213
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1098.83 lb(US) (498.42 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov