# Product data sheet

Specifications



### Circuit breaker enclosure, QO, 3 phase, 3 spaces, 100A, NEMA3R, UL

QO3100BNRB

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 207.00 USD

#### Main

Product Type	Enclosure
Range Of Product	QO
Load Center Type	Main lugs

#### Complementary

Complementary	
Current Rating	100 A
Interrupt Rating	22 kA
Number Of Spaces	3
Maximum Number Of Tandem Breakers	0
Number Of Phases	3 phase
Enclosure Rating	NEMA 3R outdoor
Breaker Compatibility	Circuit breaker QO 3P
Product Certifications	UL Listed CSA
Electrical Connection	Lugs
Surface Finish	Baked enamel Gray
Busbar Material	Tin plated copper
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Tightening Torque	35 lb.in, AWG 14AWG 10, copper 35 lb.in, AWG 12AWG 10, aluminium Main lugs 40 lb.in, AWG 8AWG 4, aluminium/copper Main lugs 50 lb.in, AWG 3AWG 2, aluminium/copper Main lugs 35 lb.in, AWG 14AWG 10, copper Main lugs 35 lb.in, AWG 12AWG 10, aluminium
Box Number	10R
Cover Type	Surface cover
Ground Bar	Grounding bar (ordered separately)
Enclosure Material	Welded galvannealed steel
Enclosure Type	Enclosure
Height	13.19 in (335 mm)
Width	6.93 in (176 mm)
Depth	4.12 in (104.65 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10DE200023
Discount Schedule	0DE2
Gtin	785901051770
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	14.49 in (36.8 cm)
Package 1 Weight	8.09 lb(US) (3.67 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov