

Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 25A, 3 pole, 120/240VAC, 10kA, plug in, Powerlink

QO325PL

Discontinued on: Sep 30, 2022

Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	25 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 120/240 V AC 10 kA 240 V AC 10 kA 120 V AC
Number Of Panel Spaces	3
Provided Equipment	18 in (457.20 mm) lead
Wire Size	AWG 12...AWG 8 aluminium AWG 14...AWG 2 copper
Tightening Torque	35.40 lbf.in (4 N.m)
Height	4.57 in (116 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.39 lb(US) (0.177 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	09650-POWERLINK QO(B)PL BREAKERS
Discount Schedule	DE8A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	785901095927
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	6.24 oz (176.901 g)

Contractual warranty

Warranty	18 months
----------	-----------