





Mini circuit breaker, QO, 30A, 3 pole, 240VAC, 10kA, plug in, 30mA grd fault B

QO330EPD

! Discontinued on: Jun 30, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product | Miniature circuit-breaker | |
|-----------------------|---------------------------------------|--|
| Range | QO | |
| Current Rating | 30 A | |
| Voltage Rating | 240 V AC | |
| Mounting Type | Plug-in | |
| Number Of Poles | 3P | |
| Circuit Breaker Type | Ground fault protecting class B 30 mA | |
| Ratings | Not rated | |
| Electrical Connection | Pressure plate | |

Complementary

| Interrupt Rating | 10 kA 240 V AC | |
|------------------------|---|--|
| Number Of Panel Spaces | 3 | |
| Wire Size | AWG 14AWG 8 copper AWG 12AWG 8 aluminium | |
| Tightening Torque | 35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4) | |
| Height | 4.13 in (105 mm) | |
| Width | 2.24 in (57 mm) | |
| Depth | 2.91 in (74 mm) | |
| Net Weight | 1.33 lb(US) (0.603 kg) | |

Environment

| Certifications | UL Listed CSA | |
|----------------|------------------|--|
| Ambient Rating | 104 °F (40 °C) | |

Ordering and shipping details

| Category | US1DE2A00910 | |
|-------------------|--------------|--|
| Discount Schedule | DE2A | |
| Gtin | 785901982739 | |
| Returnability | Yes | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.60 in (6.604 cm) |
| Package 1 Width | 3.50 in (8.89 cm) |
| Package 1 Length | 6.50 in (16.51 cm) |
| Package 1 Weight | 21.28 oz (603.278 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |