

Product data sheet

Specifications



Mini circuit breaker, QO, 30A, 3 pole, 208Y/120VAC, 10kA, plug in, 6mA grd fault A, pigtail

QO330GFI

Product availability: Stock - Normally stocked in distribution facility

Price*: 791.00 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	208Y/120 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	10 kA 208Y/120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening Torque	35.40 lbf.in (4 N.m) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in² (4...20 mm²) (AWG 12...AWG 4)
Height	4.13 in (105 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.38 lb(US) (0.626 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00103
Discount Schedule	DE2A
Gtin	785901218975
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.80 in (7.112 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	6.40 in (16.256 cm)
Package 1 Weight	22.08 oz (625.958 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov