# **Product data sheet**

Specifications



# Load center, QO, 3 phase, 30 spaces, 30 circuits, 200A convertible main breaker, NEMA3R, QDL, UL

QO330MQ200RB

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 2,147.00 USD

#### Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Surface cover

#### Complementary

Complementary	
Pon Convertible Mains (Lugs)	Main breaker
Rated Current	200 A
Number Of Spaces	30
Max Short Circuit Current Rating	25 kA
Maximum Number Of Single Pole Circuits	30
Maximum Number Of Tandem Breakers	0
Number Of Phases	3 phase 3-wire 3 phase 3 wires
Voltage Rating	208Y/120 V AC 240/120 V delta AC 240 V delta AC
Wire Size	AWG 4300 kcmil aluminium/copper
Ground Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Wiring Configuration	4-wire
Busbar Material	Tin plated copper: busbar
Enclosure Material	Welded galvannealed steel
Surface Finish	Baked enamel Gray
Box Number	14R
Height	39.37 in (1000 mm)
Width	14.76 in (375 mm)

#### Environment

Enclosure Rating	NEMA 3R weatherproof enclosure
Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

### Ordering and shipping details

Category	US10DE300017
Discount Schedule	0DE3
Gtin	785901290612
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	40.98 in (104.1 cm)
Package 1 Width	5.12 in (13.0 cm)
Package 1 Length	15.39 in (39.1 cm)
Package 1 Weight	47.00 lb(US) (21.319 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	24
Package 2 Height	45.50 in (115.57 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1155.00 lb(US) (523.899 kg)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov