

Product data sheet

Specifications

SQUARE D



Mini circuit breaker, QO, 35A, 3 pole, 240VAC, 10kA, plug in, Powerlink

QO335PL

Discontinued on: Jan 23, 2021

Discontinued

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	35 A
Voltage Rating	240 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA 240 V AC
Number Of Panel Spaces	3
Provided Equipment	18 in (457.20 mm) lead
Wire Size	AWG 12...AWG 8 aluminium AWG 14...AWG 2 copper
Height	4.57 in (116 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.16 lb(US) (0.526 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00912-POWERLINK BREAKERS
Discount Schedule	DE8A
Gtin	785901095941
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.40 in (6.096 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	18.56 oz (526.167 g)

Contractual warranty

Warranty	18 months
----------	-----------