

# Product data sheet

Specifications



Mini circuit breaker, QO, 40A, 3 pole, 208Y/120VAC, 10kA, plug in, 6mA grd fault A, pigtail

QO340GFI

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 791.00 USD

## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	40 A
Voltage Rating	208Y/120 V AC
Mounting Type	Plug-in
Number Of Poles	3P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Box lugs

## Complementary

Interrupt Rating	10 kA 208Y/120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 12...AWG 4 aluminium AWG 14...AWG 6 copper
Tightening Torque	44.25 lbf.in (5 N.m) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in² (4...20 mm²) (AWG 12...AWG 4)
Height	4.13 in (105 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.41 lb(US) (0.640 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	US1DE2A00103
Discount Schedule	DE2A
Gtin	785901979043
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	2.25 in (5.718 cm)
Package 1 Length	5.38 in (13.665 cm)
Package 1 Weight	22.56 oz (639.565 g)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>