





Load center, QO, 3 phase, 42 spaces, 42 circuits, 200A convertible main breaker, NEMA1, QDL, UL

QO342MQ200

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,027.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Order separately

Complementary

Tightening Torque	Cover 20 lb.in	
Pon Convertible Mains (Lugs)	Main breaker	
Rated Current	200 A	
Number Of Spaces	42	
Max Short Circuit Current Rating	25 kA	
Maximum Number Of Single Pole Circuits	42	
Maximum Number Of Tandem Breakers	0	
Number Of Phases	3 phase	
Voltage Rating	208Y/120 V AC 240/120 V delta AC 240 V delta AC	
Wire Size	AWG 4300 kcmil aluminium/copper	
Ground Bar	Grounding bar (ordered separately)	
Electrical Connection Lugs		
Wiring Configuration	3-wire 4-wire	
Busbar Material	Tin plated copper: busbar	
Enclosure Material	Welded sheet steel	
Surface Finish	Baked enamel Gray	
Box Number	12	
Height	39.37 in (1000 mm)	
Width	14.25 in (362 mm)	
Depth	3.82 in (97 mm)	
Net Weight	26.39 lb(US) (11.97 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US10DE300011
Discount Schedule	0DE3
Gtin	785901290568
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.13 in (10.5 cm)
Package 1 Width	14.61 in (37.1 cm)
Package 1 Length	41.02 in (104.2 cm)
Package 1 Weight	26.60 lb(US) (12.066 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	27
Package 2 Height	43.00 in (109.22 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	715.50 lb(US) (324.545 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov