





Generator panel, QO, 1 phase, 4 spaces, 8 circuits, 60A main breaker with interlock, NEMA1, surface cover door, UL

QO48M60DSGP

Product availability: Stock - Normally stocked in distribution facility

Price\*: 563.00 USD

### Main

Marketing Trade Name	QO
Product Type	Panel
Cover Type	Surface cover with door

### Complementary

Tightening Torque	Cover 20 lb.in	
Pon Convertible Mains (Lugs)	Main breaker	
Rated Current	60 A	
Number Of Spaces	4	
Max Short Circuit Current Rating	10 kA	
Maximum Number Of Single Pole Circuits	8	
Maximum Number Of Tandem Breakers	4	
Number Of Phases	1 phase	
Wire Size	AWG 8AWG 2 aluminium/copper	
Ground Bar	Grounding bar (ordered separately)	
<b>Electrical Connection</b>	Lugs	
Wiring Configuration	3-wire	
Busbar Material	Tin plated aluminium: busbar	
Enclosure Material	Welded sheet steel	
Surface Finish	Baked enamel Gray	
Box Number	4	
Height	12.56 in (319 mm)	
Width	8.90 in (226 mm)	
Depth	3.82 in (97 mm)	

### **Environment**

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications

UL Listed

### Ordering and shipping details

Category	US1DE3A00101
Discount Schedule	DE3A
Gtin	785901824343
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	14.40 in (36.576 cm)	
Package 1 Width	4.70 in (11.938 cm)	
Package 1 Length	10.70 in (27.178 cm)	
Package 1 Weight	9.44 lb(US) (4.282 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	78	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	785.00 lb(US) (356.07 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov