





Load center, QO, 1 phase, 6 spaces, 12 circuits, 100A fixed main lugs, NEMA1, door surface cover, UL

QO612L100DS

Product availability: Stock - Normally stocked in distribution facility

Price*: 90.00 USD

Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Surface cover with door

Complementary

Tightening Torque	Main lugs 50 lb.in, AWG 8, aluminium/copper Main lugs 50 lb.in, AWG 6AWG 1/0, aluminium/copper	
Pon Convertible Mains (Lugs)	Fixed Mains (lugs)	
Rated Current	100 A	
Number Of Spaces	6	
Max Short Circuit Current Rating	10 kA	
Maximum Number Of Single Pole Circuits	12	
Maximum Number Of Tandem Breakers	6	
Number Of Phases	1 phase 3-wire 1 phase 3 wires	
Voltage Rating	120/240 V AC	
Wire Size	AWG 8AWG 1 aluminium/copper	
Ground Bar	Grounding bar (ordered separately)	
Electrical Connection	Lugs	
Busbar Material	Tin plated aluminium: busbar	
Enclosure Material	Welded sheet steel	
Surface Finish	Baked enamel Gray	
Box Number	4	
Height	12.56 in (319 mm)	
Width	8.90 in (226 mm)	
Depth	3.74 in (95 mm)	

Environment

Enclosure Rating NEMA 1 indoor enclosure

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A00101 DE3A	
Discount Schedule		
Gtin	785901785620	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	14.40 in (36.576 cm)	
Package 1 Width	4.40 in (11.176 cm)	
Package 1 Length	10.70 in (27.178 cm)	
Package 1 Weight	8.29 lb(US) (3.76 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	78	
Package 2 Height	34.00 in (86.36 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	671.00 lb(US) (304.36 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov